

Software - VISU+ 2 RT 2048 RED NET WEB3 - 2402972

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Runtime license for Visu+ including redundancy function and networking and 3 web clients where the I/O data and variables in scripting are limited to 2048 bytes.

Why buy this product

- ✓ Full SCADA (Supervisory Control And Data Acquisition) function with visualization, trend representation, and alarm management
- ✓ Data logging, trend display, and recipe management
- ✓ Scripts can be created in VBA and IL
- ✓ Control coupling with OPC
- ✓ Fully scalable process diagrams for using one design on different devices and monitor sizes
- ✓ Multilingual software and projects, thanks to Unicode support and online selection
- ✓ Access protection with user management



Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 177977
GTIN	4055626177977
Weight per Piece (excluding packing)	80.000 g
Custom tariff number	85234910
Country of origin	Germany

Technical data

License information

Type of software	Visualization
Type of license	Runtime license

Functions

Software - VISU+ 2 RT 2048 RED NET WEB3 - 2402972

Technical data

Functions

Basic functions	Know-How protection and safety through encoding of projects
	Realtime database coupling with ODBC to MS ACCESS, MS EXCEL and SQL server
	FDA CFR 21 Part 11 compatible
Expanded functionality	Statistical alarm function
	Web client capability
	Redundancy function
	Advanced alarm management with SMS, FAX, e-mail and voice mail function
	Networking
	Visu+ as OPC server (DA & XL)
Number of I/O nodes	2048 I/O bytes

Hardware requirements

Hard disk	min. 1 GByte (recommended: 2 GB)
CPU	Pentium/Celeron, 1.6 GHz
Optical drive	DVD-ROM
Monitor resolution	XGA (1024 x 768)
Operating equipment	Keyboard, mouse

Software requirements

Operating systems	Windows® XP (SP3)
	Windows® Vista Business
	Windows® 7 Professional SP1 (32-Bit/64-Bit)
	Windows® 7 Ultimate SP1 (32-Bit/64-Bit)
	Windows® 8 Professional (32-Bit/64-Bit)
	Windows® 8 Enterprise (32-Bit/64-Bit)
	Windows® Server 2003
	Windows® Server 2008
	Windows® Server 2008 R2
	Windows® 10 (32-Bit/64-Bit)