

Protective hose - WP-SPIRAL PU C HF 17 - 3240858

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective hose, spring steel wire with PU coating, highly stranded

The figure shows a version of the article

Key Commercial Data

Packing unit	1 M
Minimum order quantity	10 M
Custom tariff number	39173200
Country of origin	Germany

Technical data

Dimensions

Inner diameter (f)	13.00 mm
Outside diameter	17.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Short-term temperature	120 °C

General

Color	blue
Type	Spring steel wire with PU coating
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	V2
Material	PU
Bending radius, static	13.00 mm

Standards and Regulations

Resistance to UV radiation	no
Halogen-free	yes

Protective hose - WP-SPIRAL PU C HF 17 - 3240858

Technical data

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27430304

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001177
ETIM 5.0	EC001177

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approvals submitted

Protective hose - WP-SPIRAL PU C HF 17 - 3240858

Approvals

Approval details

VDE Zeichengenehmigung 

Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>