

Hose holder with cover - WP-BASE C PA HF 21,2 BK - 3240961

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Hose holder with cover

Image shows WP-TCC PA HF 10.0
BK version

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
Weight per Piece (excluding packing)	6.4 g
Custom tariff number	39174000
Country of origin	Germany

Technical data

Dimensions

Hole diameter	6.5 mm
Diameter	21.2 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

General

Color	black
Components	Halogen-free
Flammability rating according to UL 94	V0
Material	PA

Standards and Regulations

Connection in acc. with standard	UL
Flammability rating according to UL 94	V0

Hose holder with cover - WP-BASE C PA HF 21,2 BK - 3240961

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27439208

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC000127
ETIM 5.0	EC001171

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

UL Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized 
