

Cable protection end sleeve - WP-SC HF 17 - 3241018


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



End sleeves as cable protection

RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 046356 711500
GTIN	4046356711500
Weight per Piece (excluding packing)	0.800 g
Custom tariff number	39174000
Country of origin	Germany

Technical data

Dimensions

Diameter	17 mm
Inner diameter (f)	13 mm

Ambient conditions

Ambient temperature (operation)	-10 °C ... 110 °C
---------------------------------	-------------------

General

Color	gray
Components	halogen-free
Flammability rating according to UL 94	HB
Material	PP

Cable protection end sleeve - WP-SC HF 17 - 3241018

Technical data

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27430316
eCl@ss 4.1	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27439210
eCl@ss 8.0	27439210
eCl@ss 9.0	27430316

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC002584
ETIM 5.0	EC000519
ETIM 6.0	EC000519
ETIM 7.0	EC000519

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	40141734

Accessories

Accessories

Corrugated pipe

Cable protection end sleeve - WP-SC HF 17 - 3241018

Accessories

Protective hose - WP-SPIRAL PVC C 17 - 3240851



Protective hose, spring steel wire with PVC coating, highly stranded

Protective hose - WP-SPIRAL PU C HF 17 - 3240858



Protective hose, spring steel wire with PU coating, highly stranded
