

Ink ribbon cartridge - TMP-RIBBON 110 BK 101 - 0803714

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., width: 110 mm, color: black



Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 246741
GTIN	4055626246741
Weight per Piece (excluding packing)	220.000 g
Custom tariff number	96121010
Country of origin	France

Technical data

Dimensions

Length (b)	60 m
Width (a)	110 mm

General

Color	black
Material	Polyester

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	24190105
eCl@ss 4.1	24190105

Ink ribbon cartridge - TMP-RIBBON 110 BK 101 - 0803714

Classifications

eCl@ss

eCl@ss 5.0	19029102
eCl@ss 5.1	19029102
eCl@ss 8.0	19140611
eCl@ss 9.0	19140611

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001675
ETIM 5.0	EC001675

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43211612