

Pocket Hex Wrench Set with Pouch

This folding tool set opens like a pocket knife and has 6 of the most popular sizes of hex wrenches, open end wrench, socket set, phillips & slotted screw driver. Made of nickel chrome alloy steel and comes in a handy carrying case.

Features

Nickel Chrome Steel Alloy

Sizes: 3/32", 1/8", 5/32",
3/16", 1/4", 5/16"

Wrench: 8mm, 10mm,
15mm

Sockets: 1/4", 5/16", 3/8"

Screwdrivers: #0 phillips
3/16" Slotted

Pouch: Vinyl



No. 63-15098 Pocket Hex set w/pouch

Step Taper Drill Bit

Philmore offers 2 of the most popular sizes of step-taper reamers for the service technician, installer or hobbyist. They are constructed of high carbon steel for long lasting use. For perfectly round holes in steel & aluminum chassis boxes and panels.



No. 63-1301 13 steps
1/8" to 1/2" in 1/32"
steps w/ 1/4" shank



No. 63-1925 9 steps
1/4" to 3/4" in 1/16"
steps w/ 3/8" shank

PRECISION KNIFE SET

No. 10250

This kit is a must for the hobbyist or anyone working with P.C. artwork. Very handy for many uses in the lab. Packaged in attractive four color box.

Kit Contains:

- (3) Knife Handle Sizes
- (1) Blade Holder
- (10) Assorted Blades
- Durable Solid Case for easy storing



PRECISION KNIFE

- Knurled aluminum handle
- Precision ground blade



No. 10260

No. 10265 - Package of 10 replacement blades

HEX KEY WRENCH SET

The set contains US-SAE standard hex-wrenches in the most common sizes. For set screws used in electronics assemblies, for knobs and shaft couplers as well as numerous household and automotive products. Included is a molded plastic holder to help keep your wrench set together.

Sizes included are: 5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16, and 3/8"



No. 63-10117

NUT TIGHTENING TOOL

No. NT500

Tool is specifically designed to tighten slotted knurled nuts on 3.5mm and some 2.5mm (i.e. Nos. 502JB, 502KB, 501JR, 702J and 666J).



D-SUBMINIATURE PIN INSERTION TOOL

Tool is designed for insertion and extraction of crimp type pins for D-Subminiature connectors. Tool body is made of plastic; and ends are metal.

No. D004



INSPECTION MIRROR

A 1.25" diameter magnifying mirror, similar to a dentist's mirror except that this one has ball joints for adjusting to just about any angle. Makes seeing the problems while servicing in tight spots much easier. Length - 6"

No. 63-390



NIBBLING TOOL



Unique hand-operated tool cuts metal and non-brittle plastic. Will cut any size or shape contour, starting from the edge or from a 3/8" inside hole. Tool cuts up to 18 gauge (0.046") as well as copper, brass, aluminum and plastics up to 1/16" (0.062").

No. 10150

V.35 PIN EXTRACTION TOOLS

These tools are designed to remove the pins from Cisco Systems V.35 connectors. They are made of steel construction and have a manual operated plunger which pushes the pin from the housing.



Features

- Steel Construction
- Manual Push Plunger
- Designed for V.35 Connectors

No. 61-396 For V.35 Male Pins

No. 61-395 For V.35 Female Pins

TELESCOPING MAGNETIC PICK-UP TOOL

No. 63-322

This handy magnetic pick-up tool telescopes from 4" to 16". Very strong magnetic tip. Will pickup 4 oz. weight.



SPRING HOOK TOOL

No. 63-317



The perfect tool for assembly of drive belts or assembly and disassembly of springs. One end is hook design for pulling. 2nd end is designed for pushing. Length is 8-1/2".