



MULTI-CART

Instantly Transforms Into 8 Configurations!



New Product

New Product



CART-R12 (All-Terrain) - Frame telescopes 34"-52" in length with 32" foldable sides. 10"x3" pneumatic rear wheels and 8"x2.5" pneumatic swivel casters.



CART-R10 (Max) - Frame telescopes 34"-52" in length with 32" foldable sides. 10"x3" pneumatic rear wheels and 5"x1.25" front swivel casters.



CART-R8 (Mid) - Identical to Max except with 8"x2.50" pneumatic rear wheels resulting in 20% smaller storage footprint than Max.



CART-R6 (Mini) - Frame telescopes from 28"-42.5" in length with 24" foldable sides. 8"x2.5" pneumatic rear wheels and 4"x1" front swivel casters.



CART-R2 (Micro) - Frame expands from 26"-39" in length with 25"/20" (front/rear) foldable sides. 6"x1.5" rear wheels and 4"x1" front swivel casters.



MULTI-CART

Professional 8-in-1 Equipment Carts

These patented Multi-Carts ingeniously change shape and length to carry huge amounts of equipment yet fold small for storage. They instantly transform into any of 8 configurations replacing the need for 8 different carts. The revolutionary design results in a moving machine that is very lightweight, rugged, affordable, and ergonomically efficient.

Designed for professionals where speed and efficiency is crucial, these Multi-Carts can reduce time and effort moving equipment by up to 50%. They are specifically designed to work with vehicles and airlines. 5 models are available to fit your needs.

Multi-Cart Features:



- ◆ Textured powder coat finish is extremely tough & environment friendly.
- ◆ Non-skid frame bed surface resists load slippage.
- ◆ Expandable frame adjusts to load size.
- ◆ Spring loaded wingbolts won't vibrate out.
- ◆ Caster brake.
- ◆ Stair climbers.
- ◆ Strong tube axels 43% lighter than solid steel.
- ◆ Foldable sides rotate & lock into place by pressing release cables.
- ◆ Expandable frame accommodates innumerable cargo sizes and shapes.



R12's patent-pending pneumatic swivel casters are very lightweight, strong, and have a special dampener to resist wheel wobble. They allow instant removal for travel and easy field service.



Pneumatic wheels absorb shock to delicate equipment and smoothly roll over rough surfaces. Tires have inner tubes for easy maintenance and specifically designed polymer hubs with roller bearings are up to 40% lighter than steel hub wheels.



Patent-pending concentric hole design is structurally strong yet lightweight. Soft thermoplastic tread bonded to polymer hub gives smoother & quieter ride than cheaper plastic wheels.

Replacement Parts:

R4CSTR/Y

4" G-Force Caster
Front wheel for R2 & R6

R5CSTR/Y

5" G-Force Caster
Front wheel for R8 & R10

R8CSTR/Y

8" Pneumatic Caster
Front wheel for R12

R10RWHL/Y

10" Pneumatic Wheel
Rear wheel for R10 & R12

WNGBOLT1

3/8" Wingbolt w/spring

PLATT#	LOAD CAP.	WEIGHT	SHIPPING BOX DIMENSIONS
CART-R2	350 lbs.	17 lbs.	28.5" x 17" x 6.5"
CART-R6	500 lbs.	25 lbs	30" x 18" x 8.25"
CART-R8	500 lbs.	29 lbs	35.5" x 19" x 8.25"
CART-R10	500 lbs.	31 lbs	35.5" x 19" x 8.25"
CART-R12	500 lbs.	36 lbs	35.5" x 19" x 8.25"

1-800-222-1555



www.plattcases.com

Platt Luggage, Inc. * 4051 W. 51st Street * Chicago, IL 60632

New Product

New Product