

Search Results

Evaluate
- FAQ's

How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) [Search Tips](#) 

Text Search: 'HSTT50-48-Q2'

Your search criteria matched only one product, shown below

HSTT50-48-Q2



- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
- Cross-linked, UV resistant material improves flame retardancy, chemical, and temperature resistance

For clear, add "C" to end of part number package suffix (Example HSTT05-48-QC). Contact customer service for additional color information.

^ Meets Mil Spec AMS-DTL-23053/5 Class 1(Colors), Class 2 (Clear)

▪ Part Number	HSTT50-48-Q2
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Thin Wall Polyolefin Heat Shrink
▪ Material	Flame retardant polyolefin cross-linked except clear [^]
▪ Color	Red
▪ CSA Certified	Yes
▪ Military Specification	AMS-DTL-23053/5 Class 1
▪ UL Recognized	E122770
▪ Length (ft.)	4
▪ Length (m)	1.2
▪ CE Compliant	No
▪ CE Marking	No
▪ Flammability Rating	Flame Retardant
▪ Max. Recovered I.D. (In.)	.250
▪ Max. Recovered I.D. (mm)	6.4
▪ Min. Expanded I.D. (In.)	.500
▪ Min. Expanded I.D. (mm)	12.7
▪ Nominal Diameter / Size	.500
▪ Nominal Recovered Wall Thickness (In.)	.025
▪ Nominal Recovered Wall Thickness (mm)	.6
▪ Pricing Description	Heat Shrink Thin, .50"-25Pcs/Pk
▪ Shrink Ratio	2:1
▪ Temperature Range	-67°F to 275°F (-55°C to 135°C)
▪ Min. Order UOM	PC
▪ Min. Order Qty.	25
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.