

Search Results

Evaluate

- FAQ's
- Product Bulletins
- PDFPan-Steel MS..

Design a Solution

- Catalog Cut Sheet
- PDFBT2HT Produc
- Part Drawings
- PDFBT75SDT Inst..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Application Guides
- PDFPan-Steel St..
- Operation Manuals
- PDFBT75SDT

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click  to remove) [Search Tips](#)

 **Text Search: 'BT75SDT'**

Your search criteria matched only one product, shown below

BT75SDT



- Screw drive tension mechanism provides high tension with minimal effort, reducing operator fatigue
- Heavy duty construction offers a longer service life
- Strapping side entry allows quick side entry of the strap into tool to speed installation

 Part Number	BT75SDT
 RoHS Compliance Status	RoHS directive is not applicable
 Part Description	Installation tool for use with 0.75" (19.1mm) width strapping only. Tensions and cuts strapping. Screwdriver required for buckle closure (not included).
 Color	Blue
 Pricing Description	Stainless Steel Strapping Tool
 Min. Order UOM	PC
 Min. Order Qty.	1
 BOM Qty. (# of Pkgs.)	0
 Add to Favorite Product List	e

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.