








THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



STYLE A



STYLE B



PART NUMBER	SEE DETAIL	"A" ± .062	"B"	MARKER ACROSS	TUBING COLOR	SEE STYLE
H050X025H1T	A	0.50 [12.70]	.75 [19.1]	4		
H075X025H1T	B	0.75 [19.05]	1.00 [25.4]	2		
H100X025H1T	C	1.00 [25.40]	.75 [19.1]	2	WHITE	A
H150X025H1T	D	1.50 [38.10]	1.00 [25.4]	1		
H200X025H1T	E	2.00 [50.80]	.75 [19.1]	1		
H050X025H2T	A	0.50 [12.70]	.75 [19.1]	4		
H075X025H2T	B	0.75 [19.05]	1.00 [25.4]	2		
H100X025H2T	C	1.00 [25.40]	.75 [19.1]	2	YELLOW	A
H150X025H2T	D	1.50 [38.10]	1.00 [25.4]	1		
H200X025H2T	E	2.00 [50.80]	.75 [19.1]	1		
H050X025H3T	A	0.50 [12.70]	.75 [19.1]	4		
H075X025H3T	B	0.75 [19.05]	1.00 [25.4]	2		
H100X025H3T	C	1.00 [25.40]	.75 [19.1]	2	BLACK	A
H150X025H3T	D	1.50 [38.10]	1.00 [25.4]	1		
H200X025H3T	E	2.00 [50.80]	.75 [19.1]	1		
H050X025H4T	A	0.50 [12.70]	.75 [19.1]	4		
H075X025H4T	B	0.75 [19.05]	1.00 [25.4]	2		
H100X025H4T	C	1.00 [25.40]	.75 [19.1]	2	RED	A
H150X025H4T	D	1.50 [38.10]	1.00 [25.4]	1		
H200X025H4T	E	2.00 [50.80]	.75 [19.1]	1		
H050X025H1T-B	A	0.50 [12.70]	.75 [19.1]	4		B
H075X025H1T-B	B	0.75 [19.05]	1.00 [25.4]	2		
H100X025H1T-B	C	1.00 [25.40]	.75 [19.1]	2	WHITE	B
H150X025H1T-B	D	1.50 [38.10]	1.00 [25.4]	1		
H200X025H1T-B	E	2.00 [50.80]	.75 [19.1]	1		

NOTE:
1. DIMENSIONS IN [] ARE IN MILLIMETERS.

CAD FILENAME/LAYERS 100923NG-DC-C10432/07H

PANDUIT CORP. TINLEY PARK, ILLINOIS
CUSTOMER DRAWING H***X025H*T OPTIMUM
COMPUTER PRINTABLE MIL. SPEC.
HEAT SHRINK MARKERS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .12 (XXX) ± .020
(.XX) ± .062 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
7	4/12/12	RVU		REVISED H150 PARTS TO SHOW ALL MARKERS ARE ONLY 1.5" LONG.	6731	R		
6	5/21/09	RVU		HT: .25 ± .032 WAS .250. MAT'L HSK TUBING GMUHS31, 3.5 WIDE LINER WAS GMUHS ADD "A" ± .062. ADD STYLE B VIEW FOR BULK BOX. UPDATE VIEWS.	5593	R		

DRAWN BY	RVU	MAT'L:	HEATSHRINK TUBING GMUHS31, 3.5 WIDE LINER	SCALE	NTS
DATE	8-1-06	DWG	A	DRAWING NO.	C10432
CHK'D		SIZE			