



PART NO.	
RLCBSRE-4-01	1/4 (6.4)
RLCBSRE-6-01	3/8 (9.5)
RLCBSRE-8-01	1/2 (12.7)
RLCBSRE-10-01	5/8 (15.9)



TO SNAP-LOCK IN A $.157 \pm .003$
(4.0 ± 0.08) DIA. HOLE,
IN A .062 (1.57) THK. BOARD.



TO SNAP-LOCK IN A $.213 \pm .003$ (5.41 ± 0.08)
DIA. HOLE, IN A .059 TO .065 (1.50 TO 1.65)
THK. PANEL/CHASSIS.

MATERIAL: NYLON 6/6 (RMS-01).
FLAME RETARDANT: NYLON (RMS-19).
BY SPECIAL ORDER.
2. COLOR: NATURAL.

TITLE: REVERSE LOCKING CKT. BD. SUPPORT, ENGLISH				DWG IN	CR
TOLERANCES UNLESS NOTED .XX= $\pm .010$.XXX= $\pm .015$ FRAC=1/64 ANG=1°	FILE # RLCBSRE	DWN: P.B.	APP:	FINAL	
	MAT'L: SEE NOTE	DT: 05-	DT:	PART #	PRINT
	RE: RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060		SEE TABLE	TYPE CA

C	CHANGED FILE NUMBER	SM 05.03.01
REV	DESCRIPTION	ENGR DATE