



Contact Us: 800-847-0486

Country / Language

Login / Register

Cart Total: \$0.00

Search By Keyword or Part Number



SHOPPING CART [0]

Products

Quick Order

Knowledge Center

Order Catalog

Contact Us

My Account

Home

Caps, Plugs & Masking

Push Fit Caps

Masking Caps

Flexible End Caps



Standard Flexible End Cap: 3.875 in (98.4 mm) ID, 1.500 in (38.1 mm) Height, 425 °F (218.3 °C) Max.Temp

Alliance In Stock

SKU: DM3875-1-1/2B

Flexible End Caps - Standard are suitable for a multitude of applications. The range comes in different sizes to suit Metric, BSP and UNF threads. The PVC material is flexible to ensure a tight fitting and different level of shores provides a choice in flexibility. Colours are used to differentiate the shore levels.

ECID: 1038535

Line Drawing

- **Color:** Yellow
- **Fitting Style:** Push Fit
- **Full Material:** Polyvinyl Chloride
- **Imperial/Metric:** Imperial
- **Inside Diameter:** 3.875 in (98.4 mm)
- **Inside Height:** 1.500 in (38.1 mm)
- **Material:** PVC
- **Maximum Temperature:** 425 °F (218.3 °C)

Line Drawing Legend

- **Inside Diameter:** A
- **Inside Height:** B

Customer Service
Contact Us
Knowledge Center
My Account
Order A Catalog

About Us
Overview
Careers
Distribution Sites
Free CAD Library
Free Samples

Important Info
Privacy Policy
Terms Of Purchase/Sale/Use
Press Releases
Minimum Order

Sign up for news and offers

Enter Email Address

Sign Up