

PACKAGING OF DIODE AND BRIDGE RECTIFIERS

BULK PACK

PACKAGE	PACKING CODE	EA PER BOX	INNER BOX SIZE (mm)	CARTON SIZE (mm)	EA PER CARTON	GROSS WEIGHT(Kg)
A-405	-B	1,000	194*84*21	450*220*255	50,000	15.64
BR-3/-6	-B	200	206*208*55	450*220*255	1,600	6.00 / 6.80
BR-8/-10	-B	200	236*236*50	497*251*282	2,000	12.24
BR-15/-25/-35/(W)	-B	50	203*205*57	450*220*255	400	12.50 (14.40)
DO-15	-B	500	194*84*21	450*220*255	25,000	12.74
DO-201	-B	500	300*73*40	347*320*271	12,000	15.90
DO-41	-B	1,000	194*75*21	415*220*255	50,000	16.2
HVM	-B	200	165*214*52	353*226*290	2,000	---
HVP	-B	40	236*236*40	502*251*145	240	8.80
MB-15/-25/-35(W)	-B	50	203*205*57	450*220*255	400	13.60 (14.30)
MP-15/-25/-35(W)	-B	50	203*205*57	450*220*255	400	7.7 (8.26)
R-1/-3	-B	1000 / 500	194*84*21	450*220*255	50,000 / 25,000	11.74 / 16.17
R-6	-B	200	300*73*40	347*320*271	4,800	12.93
RB-15	-B	1,000	165*252*59	347*320*271	10,000	11.6
RBU	-B	450	240*239*35	502*251*126	2,700	13.00
RC-2	-B	600	165*252*59	347*320*271	6,000	9.4
RS-1	-B	600	240*239*35	497*255*162	4,800	9.264
RS-2	-B	400	213*162*52	450*220*255	4,000	13.65
RS-4L	-B	300	230*162*52	502*251*126	1,800	11.3
RS-6/-8	-B	200	236*236*34	497*255*162	1,600	13.6 / 14.5
RS-2M	-B	600	236*236*40	502*251*145	3,600	10.28
RS-4M/-10M	-B	600	236*236*40	497*251*100	2,400	11.09
RS-6/8/15/20/25M	-B	300	230*190*46	410*243*157	1,800	13.37
WOM	-B	600	165*252*59	347*320*271	6,000	11.0

TUBE PACK

PACKAGE	PACKING CODE	EA PER BOX	INNER BOX SIZE (mm)	CARTON SIZE (mm)	EA PER CARTON	WEIGHT(Kg)
BDB	-C	2,000	450*140*84	464*305*283	12,000	14.18
D2PAK	-C	2,000	550*140*92	572*308*120	4,000	10.20
DB-1	-C	2,500	450*140*84	464*305*283	15,000	14.30
DB-LS	-C	4,000	450*140*84	464*305*283	24,000	16.45
RBU	-C	1,000	490*135*110	510*293*131	2,000	13.62
RS-1M/-2M	-C	1,350	540*118*118	560*259*144	2,700	12.03
RS-4M/-10M	-C	900	540*118*118	560*259*144	1,800	12.82
RS-6/8/15/20/25M	-C	600	490*135*110	510*293*131	1,200	13.12
(I)TO-220/TO-220(A)	-C	2,000	550*140*92	572*308*120	4,000	11.80
TO-247	-C	900	550*140*92	572*308*120	1,800	7.60