

Pushbutton, 9.1 mm, 1 NO, red



fields of application

- Mechanical and system engineering
- Model construction
- Home technology

description

Pushbutton with mounting hole diameter 9.1 mm

Pushbutton with mounting hole diameter 9.1 mm, 1 NO

technical data

➤ general

illuminated	No
Bezel color	red
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	70 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	80 °C
Soldering time for manual soldering, max.	3 sec
Soldering temperature for manual soldering	350 °C
Soldering	Manual soldering
Packaging	Box
Packaging unit	10 pcs.
net weight	1.6 g
Operating life	40,000 Cycles
Degree of protection, front side, according to DIN EN 60529	IP40
RoHS compliant	Yes

direct links

- [RAFI eCatalog](#)

REACH compliant	Yes
> mounting diameters	
Mounting hole	9.1 mm
Mounting depth	25.5 mm
Installation height	4.5 mm
Outside dimension, width	11 mm
> mechanical data	
Actuation function	momentary contact function
Operating force, max.	7 N
Operating force, min.	7 N
Operating travel, max.	2 mm
Contact function	1 NO
Contact system	Bridge contact
Contact material	Silver
Fixing	Threaded ring
Terminal on the rear	Solder terminal
Lötbarkeit	Yes
> electrical data	
Rated voltage, max.	24 V
Rated current, max.	0.1 A