

Pushbutton, 9.1 mm, 1 NO, yellow



fields of application

- Mechanical and system engineering
- Model construction
- Home technology

description

Pushbutton with mounting hole diameter 9.1 mm

Pushbutton with mounting hole diameter 9.1 mm, 1 NO

technical data

➤ general

illuminated	No
Bezel color	yellow
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	70 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	80 °C
Soldering time for manual soldering, max.	3 sec
Soldering temperature for manual soldering	350 °C
Soldering	Manual soldering
Packaging	Box
Packaging unit	10 pcs.
Operating life	40,000 Cycles
Degree of protection, front side, according to DIN EN 60529	IP40
RoHS compliant	Yes
REACH compliant	Yes

direct links

- [RAFI eCatalog](#)

> mounting diameters

Mounting hole	9.1 mm
Mounting depth	25.5 mm
Installation height	4.5 mm
Outside dimension, width	11 mm

> mechanical data

Actuation function	momentary contact function
Operating force, max.	7 N
Operating force, min.	7 N
Operating travel, max.	2 mm
Contact function	1 NO
Contact system	Bridge contact
Contact material	Silver
Fixing	Threaded ring
Terminal on the rear	Solder terminal
Lötbarkeit	Yes

> electrical data

Rated voltage, max.	24 V
Rated current, max.	0.1 A