



Schroff

Inpac, 19" chassis

Catalog Number: 10828-052

[Back To Product](#)

- Aluminum construction with die-cast front and rear frames
- For assembly with 19" components or individually with mounting plates. Max. installation space when fitting 19" components is 75 HP.
- Three rows ventilation slots in base for air inlet
- External dimensions in accordance with IEC 60297-3-101
- IP 20, in accordance with IEC 60529
- Modifications such as cutouts, different finishes or dimensions available
- Grounding/earthing kit optional
- Grounding/earthing connectors to: DIN EN 50178/VDE 0160, DIN EN 60950/VDE 0805, DIN EN 61010-1/VDE 0411 part 1, DIN EN 61010-1A2/VDE 0411 part 1/A1



Change Item >

CHANGING AN ITEM WILL UPDATE THE CATALOG NUMBER. THIS CAN AFFECT THE LIST PRICE AND SPECIFICATION OF THE ITEM.

Other Views



Quantity

1

Add Item to Project List ➕

Description

Downloads

Technical Data

Accessories

Downloads (1 - 5 of 5)

Documents



Main Catalog - Inpac



Measurement of electromagnetic shielding effectiveness



User Manual



Approval for the Russian market

Links



Native CAD files

EXPLORE

- About Us
- Services & Capabilities
- News & Events
- Strategic Partnerships
- Investor Relations

CONTACT

- Customer Service
- Find a Sales Office or Distributor
- Global Locations
- Product Compliance & Certifications
- Partner Login

DOWNLOAD

- Literature
- White Papers & Case Studies
- Videos & Mobile Apps
- Product Configurators
- Warranties