


(2.54 mm) .100"

THROUGH-HOLE .025" SQ POST SOCKET




Note:

Some lengths, styles and options are non-standard, non-returnable.

-RA


(2.54) .100 x No. of Spaces





Straight Pin Versions (Specify "LEAD STYLE" from chart)


LEAD STYLE		SINGLE DOUBLE	
Standard Insertion			
Force	Force*	Α	
-01	-21	(2.64) .104	
-02	-22	(4.93) .194	
-03	-23	(10.00) .394	
-04	-24	(14.83) .584	
-06**	Not Available	(3.15) .124	

^{*} LIF not available with Tin Plating **Style –06 Not available with SSQ












Right-Angle Versions (Specify "LEAD STYLE" from chart)

LEAD STYLE		SINGLE	DOUBLE	TRIPLE
Standard	Low	(-S)	(–D)	(-T & -Q)
Insertion Force	Insertion Force*	Α	Α	Α
-02	-22	(2.54) .100	(2.54) .100	(2.54) .100
-03	-23	(7.62) .300	(7.62) .300	Not Available
-04	-24	(12.45) .490	Not Available	Not Available

*LIF not available with Tin Plating







Due to technical progress, all designs, specifications and components are subject to change without notice