

Non-Insulated Ferrule Terminals

Cat. No.	Conductor Section		Dimensions (Inches / MM)				Installation Tooling	Pkg. Qty.
	AWG	MM²	C	D	A	E		
F9000	24	.25	.030 / 0.75	.067 / 1.7	.196 / 5	.006 / 0.15	T1, ERG4	1000
F9001	22	.50	.039 / 1.0	.083 / 2.1	.236 / 6	.006 / 0.15	T1, T3, ERG4	1000
F9002	22	.50	.039 / 1.0	.083 / 2.1	.394 / 10	.006 / 0.15	T1, T3, ERG4	100
F9003	18	.75	.047 / 1.2	.091 / 2.3	.236 / 6	.006 / 0.15	T1, T3, ERG4	1000
F9004	18	.75	.047 / 1.2	.091 / 2.3	.394 / 10	.006 / 0.15	T1, T3, ERG4	1000
F9005	18	1.0	.055 / 1.4	.098 / 2.5	.236 / 6	.006 / 0.15	T1, T3, ERG4	1000
F9006	18	1.0	.055 / 1.4	.098 / 2.5	.394 / 10	.006 / 0.15	T1, T3, ERG4	1000
F9007	16	1.5	.067 / 1.7	.110 / 2.8	.276 / 7	.006 / 0.15	T1, T3, ERG4	1000
F9008	16	1.5	.067 / 1.7	.110 / 2.8	.394 / 10	.006 / 0.15	T1, T3, ERG4	1000
F9009	16	1.5	.067 / 1.7	.110 / 2.8	.473 / 12	.006 / 0.15	T1, T3, ERG4	1000
F9010	16	1.5	.067 / 1.7	.110 / 2.8	.709 / 18	.006 / 0.15	T1, T3, ERG4	1000
F9011	14	2.5	.087 / 2.2	.139 / 3.4	.276 / 7	.006 / 0.15	T1, T3, ERG4	1000
F9012	14	2.5	.087 / 2.2	.139 / 3.4	.394 / 10	.006 / 0.15	T1, T3, ERG4	1000
F9013	14	2.5	.087 / 2.2	.139 / 3.4	.472 / 12	.006 / 0.15	T1, T3, ERG4	1000
F9014	14	2.5	.087 / 2.2	.139 / 3.4	.709 / 18	.006 / 0.15	T1, T3, ERG4	1000
F9015	12	4.0	.110 / 2.8	.158 / 4	.354 / 9	.008 / 0.2	T3, ERG4	1000
F9016	12	4.0	.110 / 2.8	.158 / 4	.472 / 12	.008 / 0.2	T3, ERG4	1000
F9017	12	4.0	.110 / 2.8	.158 / 4	.591 / 15	.008 / 0.2	T3, ERG4	1000
F9018	12	4.0	.110 / 2.8	.158 / 4	.709 / 18	.008 / 0.2	T3, ERG4	1000
F9019	10	6.0	.138 / 3.5	.185 / 4.7	.472 / 12	.008 / 0.2	T3, ERG4	250
F9020	10	6.0	.138 / 3.5	.185 / 4.7	.591 / 15	.008 / 0.2	T3, ERG4	250
F9021	10	6.0	.138 / 3.5	.185 / 4.7	.709 / 18	.008 / 0.2	T3, ERG4	250
F9022	8	10.0	.177 / 4.5	.228 / 5.8	.472 / 12	.008 / 0.2	T3, ERG4	250
F9023	8	10.0	.177 / 4.5	.228 / 5.8	.591 / 15	.008 / 0.2	T3, ERG4	250
F9024	8	10.0	.177 / 4.5	.228 / 5.8	.709 / 18	.008 / 0.2	T3, ERG4	250
F9025	6	16.0	.228 / 5.8	.295 / 7.5	.472 / 12	.008 / 0.2	T3, ERG4	250
F9026	6	16.0	.228 / 5.8	.295 / 7.5	.591 / 15	.008 / 0.2	T3, ERG4	250
F9027	6	16.0	.228 / 5.8	.295 / 7.5	.709 / 18	.008 / 0.2	T3, ERG4	250
F9028	6	16.0	.228 / 5.8	.295 / 7.5	.984 / 25	.008 / 0.2	T3, ERG4	250
F9029	6	16.0	.228 / 5.8	.295 / 7.5	1.26 / 32	.008 / 0.2	T3, ERG4	250
F9030	4	25.0	.287 / 7.3	.374 / 9.5	.591 / 15	.010 / .25	ERG4	1000
F9031	4	25.0	.287 / 7.3	.374 / 9.5	.709 / 18	.010 / .25	ERG4	1000
F9032	4	25.0	.287 / 7.3	.374 / 9.5	.984 / 25	.010 / .25	ERG4	1000
F9033	4	25.0	.287 / 7.3	.374 / 9.5	1.26 / 32	.010 / .25	ERG4	1000
F9034	2	35.0	.327 / 8.3	.433 / 11	.709 / 18	.010 / .25	ERG4	100
F9035	2	35.0	.327 / 8.3	.433 / 11	.984 / 25	.010 / .25	ERG4	100
F9036	2	35.0	.327 / 8.3	.433 / 11	1.26 / 32	.010 / .25	ERG4	100
F9037	1/0	50.0	.406 / 10.3	.512 / 13	.709 / 18	.012 / 0.3	ERG4	100
F9038	1/0	50.0	.406 / 10.3	.512 / 13	.984 / 25	.012 / 0.3	ERG4	100
F9039	1/0	50.0	.406 / 10.3	.512 / 13	1.18 / 30	.012 / 0.3	ERG4	100

