



Actual

**Catalog Number:** F4021  
**Product ID:** 7TAI029790R0036  
**UPC Number:** 78621033675  
**Status:** Active

Polypropylene-Insulated Old DIN Ferrule, Total Length .571 Inches/14.5mm, Pin Length .315 Inches/8mm, Pin Diameter .043 Inches/1.1mm, Base Diameter .102 Inches/2.6mm, Wire Range #20 AWG/.50mm<sup>2</sup>, Color White, Copper, Tin Plated

- Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
- Application Tools: T1, T3, ERG4

**North American Specifications (UNSPSC)**

|                  |                                                                                                             |
|------------------|-------------------------------------------------------------------------------------------------------------|
| UNSPSC           | 39121432 Electrical terminals                                                                               |
| IGCC             | 4603 Electrical terminals                                                                                   |
| Brand Name       | Sta-Kon                                                                                                     |
| Type             | Ferrule                                                                                                     |
| Special Features | Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks. |
| Wire Size        | 20                                                                                                          |
| Material         | Copper                                                                                                      |
| Color            | White                                                                                                       |

**European Specifications (ETIM)**

|                       |                           |
|-----------------------|---------------------------|
| ETIM                  | EC000005 Cable end sleeve |
| Nominal cross section | 0.5mm <sup>2</sup>        |
| Insulated             | Y                         |
| Insulation material   | Polypropylene             |
| Colour                | White                     |
| Material              | Copper                    |
| Surface protection    | Tinned                    |
| Reel packaging        | N                         |

**Packaging**

|                |                    |
|----------------|--------------------|
| Inner Quantity | 500                |
| Outer Quantity | 10000              |
| Weight Uom     | 4.38 lbs. per 1000 |

**Documents / Support Tools**

|                             |                      |
|-----------------------------|----------------------|
| Technical Data Sheet CA     | Available on Website |
| Technical Data Sheet Global | wsd-000402           |

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com