



Identification Tie T&B Catalog Number:

TY53M
78621082534
Active

UPC Number: Status: Description:

Identification Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 101.6mm (4 Inches), Width of 2.53mm (1.0 Inches), Thickness of 1.18mm (0.046 inches), Marking Pad Size of 20.24mm (0.80 Inches) x 0.356mm (9.04 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack

General

Material	Nylon 6.6
Color	Natural

Dimension Information

Nominal Length (inches)	4
Length (inches)	4
Width (inches)	.093
Max. Wire Bundle Diameter (inches)	.625
Marking Pad Size	.813 x .359

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Packaging

T&B Order Multiple	500
T&B Inner Pack	500
Package in Units	5000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	1.25 lbs. per 1000

Application Support

Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications

RoHS Compliance	Yes
Webcat CE_recognized	Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com