



Actual

Catalog Number: F2052
Product ID: 7TAI029790R0024
UPC Number: 78621033556
Status: Active

Polypropylene-Insulated Ferrule, Total Length 1.535 Inches/39mm, Pin Length .984 Inches/25mm, Pin Diameter .335 Inches/8.5mm, Base Diameter .492 Inches/12.5mm, Wire Range 2 AWG/35.00mm², Color Red, Copper, Tin Plated

- Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
- Application Tools: ERG4

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ferrule
Special Features	Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
Standard	UL E489056
Wire Size	2
Material	Copper
Color	Red

European Specifications (ETIM)

ETIM	EC000005 Cable end sleeve
Construction type	Standard
Nominal cross section	35mm ²
Insulated	Y
Insulation material	Polypropylene
Colour	Red
Material	Copper
Surface protection	Tinned
With identification flag	N
Reel packaging	N

Packaging

Inner Quantity	50
Outer Quantity	500
Outer Dimensions (inches)	10x8x4.75
Weight Uom	3.13 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com