

EXTERNAL SIREN FOR CONCEALED INSTALLATION



Outdoor siren for concealed installation.

Specifications

- operating power: 10 - 14Vdc / 150mA max.
- siren output: 120dB
- power cord: 27cm (± 10%)
- can easily be affixed to a wall
- operating frequency: 2.4kHz - 3.7kHz (± 30%)
- operating temperature: -20°C to +60°C max. (10 min.)
- colour: ivory
- dimensions: 122 x 72 x 35mm
- weight: 100g

All registered trademarks and trade names are properties of their respective owners and are used only for the clarification of the compatibility of our products with the products of the different manufacturers.

Due to constant product improvements the actual product appearance might differ from the shown images. Product images are for illustrative purposes only.

[REACH communicating information according to article 33](#)
[WEEE](#)

