

Log on
[Log on as distributor](#)



Vatican City State - English (UK)
[Change](#)

Search product

[Search](#) [Advanced](#)

[PRODUCT OVERVIEW](#) [ADAPTERS & POWER SUPPLIES](#) [DC CONNECTORS AND PLUGS](#)

DC PLUG 5.5x2.5MM FEMALE TO SCREW TERMINAL (5pcs)



CD015
Support
[Labelsheet](#)
[Support](#)

- Navigation
- Main page
 - Products
 - Sales outlets
 - Support
 - Publications
 - Jobs
 - About us

News

NEW MK193 LED CUBE

CubeAnimator software available for download here!!

Posted on 04-06-12
[Read more...](#)

New Ring scanners

Velleman invests again in its logistics system.

Posted on 14-05-12
[Read more...](#)

Glass Touch Panels

Glass Touch Panels with or without OLED. Coming soon.

Posted on 04-04-12
[Read more...](#)

New cable range

Discover our new audio, video & computer cables range!

Posted on 12-03-12
[Read more...](#)

PROLYTE Product news

Due to its recent increased raw material costs, Prolyte...

Posted on 19-07-11
[Read more...](#)

Features

- female to removable screw

Specifications

- max. voltage: 25V
- max. current: 4A
- max. operating temperature: 30°C

All registered trademarks and trade names are properties of their respective owners and are used only for the clarification of the compatibility of our products with the products of the different manufacturers. Due to constant product improvements the actual product appearance might differ from the shown images. Product images are for illustrative purposes only.

[REACH communication information according to article 33 WEEE](#)

© 2012
All rights reserved
[Sitemap](#) | [Disclaimer](#) | [RSS-Feeds](#)

- [velleman.eu](#)
- [happower.eu](#)
- [parel.eu](#)
- [vullemanproject.com](#)
EU - modules - instruments
- [velbus.eu](#)
- [forum.velleman.eu](#)

Advertisements

Subscribe to our NEWSLETTER