

Search Product:

Submit

[[Advanced](#)]

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)

[ROHS Info](#)

[BATTERIES & CHARGERS](#) > [BATTERY CHARGERS](#) > [BATTERY CHARGERS FOR NICD & NIMH BATTERIES](#) >



5-IN - 1 USB NiMH AAA CHARGER AND POWER PACK

Order Code: VL118USB



Features

- ? the ideal power pack for use with your portable music player
- ? charge the power pack and use it as a portable power supply
- ? charging via PC or car adapter with 5VDC USB output
- ? instant power through USB
- ? torch with bright LED
- ? 2 individual charging channels
- ? 6 levels of protection:
 - ? negative delta (-dV)
 - ? cutoff after charging time of 3h40
 - ? temperature sensor
 - ? reverse polarity protection
 - ? short-circuit protection
 - ? defective or non-rechargeable batteries detection
- ? can be used with following battery types: 4 x HR3C/11(not incl.) or 4 x HR3C(not incl.)

Specifications

- ? power pack input: 5VDC (USB powered)
- ? power pack output: 2 x 2.8VDC / 300mA
- ? USB output: 5VDC / 1A (USB2.0)
- ? car adapter input: 12VDC / 650mA
- ? car adapter output: 5VDC / 1A
- ? charging time:
 - ? NiMh AAA 1000mAh: 3.2h
 - ? NiMH AAA 600mAh: 2.0h
- ? operating temperature: 32° F ~ 77°F
- ? storage temperature (batteries excluded): -4°F ~ 149°F
- ? dimensions:
 - ? power back: 2 11/64" x 3 15/32" x 55/64"
 - ? car adapter: 100 x 42 x 20mm
- ? total weight (without batteries): 7.4 oz

Files

- ? [EN- FR- NL- ES- DE](#)

Stock Info

- ? Inner carton:
- ? Outer Carton:
- ? EAN Barcode: 5410329379858
- ? Packaging: Double Blister