

Accessories
TS 15X5/LL 2M/ST/ZN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**General ordering data**

Type	TS 15X5/LL 2M/ST/ZN
Order No.	0117500000
Version	Rail, TS 15, with slot, Steel, galvanic zinc plated and passivated
GTIN (EAN)	4008 190150662
Qty.	2 m

Creation date August 22, 2020 1:58:18 AM CEST

Catalogue status 14.08.2020 / We reserve the right to make technical changes.

Accessories TS 15X5/LL 2M/ST/ZN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	15 mm	Width (inches)	0.591 inch
Height	5.5 mm	Height (inches)	0.217 inch
Depth	5.5 mm	Depth (inches)	0.217 inch
Net weight	140 g		

Mounting rail

Drill-hole diameter	4.2 mm	Short circuit strength corresponds to E-Cu wire	10 mm ²
Short-time withstand current according to IEC 60947-7-2	1.2 kA/1s	Slit gap	8 mm
Slit length	12 mm	Slit width	4.2 mm
Slotted drill holes	Yes	Solder eyelet hole diameter (D)	4.2 mm
Spacing of holes, centre-to-centre	20 mm	Thickness	1 mm

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
eClass 9.0	27-40-06-02	eClass 9.1	27-40-06-02
eClass 10.0	27-40-06-02	UNSPSC	30-21-18-01

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
User Documentation	StorageConditionsTerminalBlocks