

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1210120095

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Base, Form A-18mm, B28 Base, 2 Pole Plus Ground Terminal, 250V AC/300V DC, Black, Nitrile Gasket with Screw

Documents:

Drawing (PDF)

Packaging Specification PK-121012-B28-001 (PDF)

Test Summary STR-1467-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Form

IP Rating

Material - Contact

Overview

Product Name

Type

UPC

Field Attachable / Accessories

121012

A - 18mm

IP65, IP67

Brass

mPm DIN Valve Connectors

mPm

Field Attachable Connector

883906361068

Physical

Cable Diameter

Coupling Type

Diagnostics / LEDs

Diagnostics Port

Gender

Keyway

Material - Connector Body

Material - Coupling Nut

Material - Plating Mating

Net Weight

Orientation

Pitch - Mating Interface

Poles

Temperature Range - Operating

Wire Size AWG

N/A

N/A

No

No

N/A

None

Polypropylene

N/A

Silver

10.024/g

Straight

18.00mm

2

-40°C to +90°C

N/A

Electrical

Current - Maximum per Contact

Voltage - Maximum

16.0A

250V AC / 300V DC

Material Info

Engineering Number

B282000N2

Reference - Drawing Numbers

Packaging Specification

Sales Drawing

Test Summary

PK-121012-B28-001

SD-121012-003

STR-1467-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

121012 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION