

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300990076

Status:

Active

Overview:

Strain-Relief Cord Grips

Description:

MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, Straight Male, Cable Diameter 7.93-9.53mm (.312-.375"), Stainless Steel Mesh



Series image - Reference only

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

Agency Certification	
CSA	LR32159
General	
Product Family	Cable Grips
Series	130099
Exclude SD Check	Yes
Eye Type	N/A
NEMA Rating	NEMA 3R
O-Ring	No
Overview	Strain-Relief Cord Grips
Product Literature Order No	987651-6081
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678855264
Use With	1/2" NPT MAX-LOC Lock Nut 1300990143 , MAX-LOC O-Ring, 1/2" NPT 1301800314 , 1/2" NPT MAX-LOC Gasket 1300990149
Physical	
Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	7.93-9.53mm (.312-.375")
Color - Grommet	Gray
Gender	Male
Material - Body	Nylon
Material - Grip	Stainless Steel
Mesh Length	N/A
Number of Holes	1
Thread Size	1/2" NPT
Material Info	
Engineering Number	5526M
Reference - Drawing Numbers	
Sales Drawing	SD-130099-003

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130099 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION