

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301280140

Status:

Active

Description:

Heavy Duty Stranded Cable, Type SOW-SOW-A, 16 AWG, 4 Conductors, 76.20m Length, Yellow

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable
Series	130128
Crimp Quality Equipment	Yes
Product Name	Heavy Duty
UPC	78678879960
Physical	
Cable Length	76.20m
Circuits (Loaded)	4
Color - Cable Jacket	Yellow
Insulation	EP Rubber
Net Weight	53.977/g
Outer Jacket Diameter	10.41mm
Packaging Type	Carton
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	16
Wire/Cable Type	SOW, SOW-A
Electrical	
Current - Maximum per Contact	8.0A
Voltage - Maximum	600V
Material Info	
Engineering Number	SY16-4

Image coming soon

Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130128 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION