

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301370087](#)  
**Status:** **Active**  
**Overview:** [Outlet Boxes](#)  
**Description:** Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, Cord Clamp, Duplex Cover Plates only

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837  
 UL      E46237

**General**

Product Family      Power Distribution  
 Series      [130137](#)  
 Enclosure Rating      NEMA 4  
 Exclude SD Check      Yes  
 GFCI Reset      N/A  
 Mounting Style      Portable  
 Open Neutral Relay      N/A  
 Overview      [Outlet Boxes](#)  
 Product Literature Order No      987650-7737  
 Product Name      Super-Safeway  
 Receptacle Type      Duplex  
 Type      Multiple Outlet Box  
 UPC      78678875050

**Physical**

Cord Diameter      8.26-16.64mm (.325-.655")  
 Cord Grip Body Size      F3 3/4"  
 Cord Length      N/A  
 Feed-Thru      No  
 Flip Lid      Yes  
 Material - Housing      Rubber  
 Net Weight      420.026/g  
 Number of Receptacles      2 - Customer Supplied  
 Packaging Type      Carton

**Electrical**

Cord Type      N/A  
 Current - Maximum per Contact      Per Cust. Supplied Receptacle  
 GFCI      No  
 Ground Continuity Monitor      No  
 NEMA Configuration      N/A  
 Voltage - Maximum      Per Cust. Supplied Receptacle

**Material Info**

Engineering Number      3000



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

**China RoHS**

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130137 Series](#)