

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370130](#)
Status: **Active**
Overview: [Watertite Wet-Location Wiring Solutions](#)
Description: Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, F2 (1/2"), NEMA 5-15 Duplex Receptacles with Flip Lids, 15.24m (50.0') Cord Length, 14/3 SOOW Cord, 5-15 Plug

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
UL E38085

General

Product Family Power Distribution
Series [130137](#)
Enclosure Rating NEMA 4
Exclude SD Check Yes
GFCI Reset N/A
Mounting Style Portable
Open Neutral Relay N/A
Overview [Watertite Wet-Location Wiring Solutions](#)
Product Literature Order No 987650-7737
Product Name Super-Safeway
Receptacle Type Duplex
Type Multiple Outlet Box
UPC 78678879664

Physical

Cord Diameter 13.59mm (.535")
Cord Grip Body Size F2 1/2"
Cord Length 15.24m (50.0')
Feed-Thru No
Flip Lid Yes
Material - Housing Rubber
Number of Receptacles 2
Packaging Type Carton

Electrical

Cord Type 14/3 SOOW
Current - Maximum per Contact 15.0A
GFCI No
Ground Continuity Monitor No
NEMA Configuration NEMA 5-15
Voltage - Maximum 125V

Material Info

Engineering Number 3005-1B143



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130137](#) Series