

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301370132](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, F2 (1/2"), NEMA 5-15 Duplex Receptacles with Flip Lids, 0.305m (1.0') Cord Length, 14/3 SOOW Cord, 5-15 Plug

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA	LR6837
UL	E38085

**General**

Product Family	Power Distribution
Series	<a href="#">130137</a>
Enclosure Rating	NEMA 4
Exclude SD Check	Yes
GFCI Reset	N/A
Mounting Style	Portable
Open Neutral Relay	N/A
Overview	<a href="#">Watertite Wet-Location Wiring Solutions</a>
Product Literature Order No	987650-7737
Product Name	Super-Safeway
Receptacle Type	Duplex
Type	Multiple Outlet Box
UPC	78678879662

**Physical**

Cord Diameter	13.59mm (.535")
Cord Grip Body Size	F2 1/2"
Cord Length	0.305m (1.0')
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Number of Receptacles	2
Packaging Type	Carton

**Electrical**

Cord Type	14/3 SOOW
Current - Maximum per Contact	15.0A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-15
Voltage - Maximum	125V

**Material Info**

Engineering Number	3005-1E143
--------------------	------------



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130137 Series](#)