

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301370171](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Super-Safeway Multiple Outlet Box, Extended Depth, 2-Sided, NEMA 5-20, Cord Clamp, Duplex Cover Plates, 0.305m (1.0') Cord Length, 12/3 SOOW Cord, 5-20 Plug

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA	LR6837
UL	E38085

**General**

Product Family	Power Distribution
Series	<a href="#">130137</a>
Enclosure Rating	N/A
Exclude SD Check	Yes
GFCI Reset	N/A
Mounting Style	Portable
Open Neutral Relay	N/A
Overview	<a href="#">Watertite Wet-Location Wiring Solutions</a>
Product Literature Order No	987650-7737
Product Name	Super-Safeway
Receptacle Type	Duplex
Type	Multiple Outlet Box
UPC	78678875097

**Physical**

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	Double C-Clamp
Cord Length	0.305m (1.0')
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber
Number of Receptacles	2
Packaging Type	Carton

**Electrical**

Cord Type	12/3 SOOW
Current - Maximum per Contact	20.0A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-20
Voltage - Maximum	125V

**Material Info**

Engineering Number	3080-10E123
--------------------	-------------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

**China RoHS**

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130137 Series](#)