

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430159

Status:

Active

Overview:

Watertite Wet-Location Wiring Solutions

Description:

Watertite Cordset 14 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA L6-15, 250V



Documents:	
RoHS Certificate of Compliance (PDF)	Product Literature (PDF)
Agency Certification	
CSA	LR6837
UL	E38085
General	
Product Family	Wiring Devices
Series	130143
Exclude SD Check	Yes
IP Rating	IP67
NEMA Configuration	NEMA 6-15
Overview	Watertite Wet-Location Wiring Solutions
Product Literature Order No	987650-8067
Product Name	Watertite
Receptacle Type	Single
Specialty	N/A
Type	Cordset
UPC	78678871032
Physical	
Cord Grip Body Size	F2 1/2"
Flange	No
Flip Lid	No
Gender	Male-Female
Length	15.24m (50.0')
Locking Blade	No
Poles	2-pole/3-wire
Electrical	
Cord Type	12/3 SOOW
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	250V
Material Info	
Engineering Number	14W49B143

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION