

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430254

Status:

Active

Overview:

Heavy-Duty Industrial Wiring Devices

Description:

Super-Safeway Cordset, 10 Gauge SOOW, 2 Pole/3 Wire, Cordset, Length 7.62m (25.0'), NEMA L6-30, 250V



Documents:	
RoHS Certificate of Compliance (PDF)	Product Literature (PDF)
Agency Certification	
CSA	LR6837
UL	E38085
General	
Product Family	Wiring Devices
Series	130143
Exclude SD Check	Yes
IP Rating	N/A
NEMA Configuration	NEMA L6-30
Overview	Heavy-Duty Industrial Wiring Devices
Product Literature Order No	987650-8068
Product Name	Super-Safeway
Receptacle Type	Single
Specialty	N/A
Type	Cordset
UPC	78678804183
Physical	
Flange	No
Flip Lid	No
Gender	Male-Female
Length	7.62m (25.0')
Locking Blade	Yes
Poles	2-pole/3-wire
Electrical	
Cord Type	10/3 SOOW
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	250V
Material Info	
Engineering Number	2848A103

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION