

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301460155](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Male Receptacle with Flip Coverplate, 2 Pole/2 Wire, NEMA-L2-20, 250V

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                             |   |
|-----------------------------|---|
| Product Family              | Wiring Devices  |
| Series                      | <a href="#">130146</a>                                  |
| Exclude SD Check            | Yes   |
| IP Rating                   | IP67  |
| NEMA Configuration          | NEMA L2-20  |
| Overview                    | <a href="#">Watertite Wet-Location Wiring Solutions</a> |
| Product Literature Order No | 987650-8067   |
| Product Name                | Watertite   |
| Receptacle Type             | N/A   |
| Specialty                   | N/A   |
| Type                        | Inlet   |
| UPC                         | 78678871445   |

**Physical**

|               |               |
|---------------|---------------|
| Flange        | No            |
| Flip Lid      | No            |
| Gender        | Male          |
| Length        | N/A           |
| Locking Blade | Yes           |
| Poles         | 2-pole/2-wire |

**Electrical**

|                               |       |
|-------------------------------|-------|
| Cord Type                     | N/A   |
| Current - Maximum per Contact | 20.0A |
| GFCI                          | No    |
| Lighted Connector             | No    |
| Voltage - Maximum             | 250V  |

**Material Info**

|                    |       |
|--------------------|-------|
| Engineering Number | 66W07 |
|--------------------|-------|

**Reference - Drawing Numbers**

|               |                |
|---------------|----------------|
| Sales Drawing | 1301460155-000 |
|---------------|----------------|



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130146 Series](#)