

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301530030

Status:

Active

Overview:

Ground Fault Circuit Interrupter (GFCI) Products

Description:

Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Manual Reset, Molded NEMA 5-15 Plug and Tri-Tap Connector, 15A, 120V, 0.61m (2.0') Cord Length



Documents:

[Drawing \(PDF\)](#)

[Product Literature \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E66308
General	
Product Family	Power Distribution
Series	130153
Enclosure Rating	NEMA 3R
Exclude SD Check	Yes
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	Ground Fault Circuit Interrupter (GFCI) Products
Product Literature Order No	987650-7737
Product Name	Super-Safeway
Receptacle Type	N/A
Type	GFCI Industrial Duty, Single Phase
UPC	78678889750
Physical	
Cord Diameter	10.92mm (.430")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Net Weight	620.513/g
Number of Receptacles	3
Packaging Type	Bag
Electrical	
Cord Type	12/3 SJTW
Current - Maximum per Contact	15.0A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-15
Voltage - Maximum	120V
Material Info	
Engineering Number	15050-3TTM
Reference - Drawing Numbers	
Sales Drawing	SD-130153-014

EU ELV

Not Relevant

EU RoHS

Not Relevant

China RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Not Relevant

Status

Not Relevant

For more information, please visit

Contact US

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130153 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION