

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530042](#)
Status: **Active**
Overview: [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
Description: Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, NEMA 5-15, 15A, 120V, 0.61m (2.0') Cord Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
UL E66308

General

Product Family Power Distribution
Series [130153](#)
Enclosure Rating NEMA 4
Exclude SD Check Yes
GFCI Reset Manual
Mounting Style Portable
Open Neutral Relay Yes
Overview [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
Product Literature Order No 987650-7737
Product Name Safeway
Receptacle Type N/A
Type GFCI Commercial Duty, Single Phase
UPC 78678828405

Physical

Cord Diameter 9.40mm (.370")
Cord Grip Body Size Internal Double C-Clamp
Cord Length 0.61m (2.0')
Feed-Thru Yes
Flip Lid No
Material - Housing Nylon
Number of Receptacles 1
Packaging Type Bag

Electrical

Cord Type 14/3 SJTW
Current - Maximum per Contact 15.0A
GFCI Yes-In-line
Ground Continuity Monitor No
NEMA Configuration NEMA 5-15
Voltage - Maximum 120V AC

Material Info

Engineering Number 15051-1



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130153](#) Series