

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530079](#)
Status: **Active**
Overview: [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
Description: Super-Safeway Right-Angle Industrial GFCI, Portable, Single Phase, Manual Reset, Outlet Box, NEMA 5-15 Double Duplex, 15A, 120V, 15.24m (50.0') Cord Length

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E66308

General

Product Family Power Distribution
Series [130153](#)
Enclosure Rating NEMA 3R
Exclude SD Check Yes
GFCI Reset Manual
Mounting Style Portable
Open Neutral Relay Yes
Overview [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
Product Literature Order No 987650-7737
Product Name Super-Safeway
Receptacle Type Duplex
Type GFCI Industrial Duty, Single Phase
UPC 78678889766

Physical

Cord Diameter 10.92mm (.430")
Cord Grip Body Size Internal Double C-Clamp
Cord Length 15.24m (50.0')
Feed-Thru Yes
Flip Lid No
Material - Housing Nylon
Number of Receptacles 2
Packaging Type Carton

Electrical

Cord Type 12/3 SJTW
Current - Maximum per Contact 15.0A
GFCI Yes-In-line
Ground Continuity Monitor No
NEMA Configuration NEMA 5-15
Voltage - Maximum N/A

Material Info

Engineering Number 15053-50M

Reference - Drawing Numbers

Sales Drawing SD-130153-019



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130153](#) Series