

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301530111

Status:

Active

Overview:

Ground Fault Circuit Interrupter (GFCI) Products

Description:

Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, Flying Leads, 20A, 120V, 0.61m (2.0') Cord Length



Series image - Reference only

Documents:	
RoHS Certificate of Compliance (PDF)	Product Literature (PDF)
Agency Certification	
CSA	LR6837
UL	E66308
General	
Product Family	Power Distribution
Series	130153
Enclosure Rating	NEMA 4
Exclude SD Check	Yes
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	Ground Fault Circuit Interrupter (GFCI) Products
Product Literature Order No	987650-7737
Product Name	Safeway
Receptacle Type	N/A
Type	GFCI Commercial Duty, Single Phase
UPC	78678828417
Physical	
Cord Diameter	10.92mm (.430")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Number of Receptacles	0
Packaging Type	Bag
Electrical	
Cord Type	12/3 SJTW
Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	N/A
Voltage - Maximum	120V AC
Material Info	
Engineering Number	20051-1

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130153 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION