

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530128](#)
Status: **Active**
Overview: [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
Description: Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, NEMA 5-20, 20A, 120V, 7.62m (25.0') Cord Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E66308

General

Product Family Power Distribution
Series [130153](#)
Enclosure Rating NEMA 4X
Exclude SD Check Yes
GFCI Reset Automatic
Mounting Style Portable
Open Neutral Relay Yes
Overview [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
Product Literature Order No 987650-7737
Product Name Super-Safeway
Receptacle Type N/A
Type GFCI Industrial Duty, Single Phase
UPC 78678888293

Physical

Cord Diameter 10.67mm (.420")
Cord Grip Body Size Internal Double C-Clamp
Cord Length 7.62m (25.0')
Feed-Thru Yes
Flip Lid No
Material - Housing Nylon
Number of Receptacles 1
Packaging Type Bag

Electrical

Cord Type 12/3 SJEOOW
Current - Maximum per Contact 20.0A
GFCI Yes-In-line
Ground Continuity Monitor No
NEMA Configuration NEMA 5-20
Voltage - Maximum N/A

Material Info

Engineering Number 20052-25A



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130153](#) Series