

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530184](#)
Status: **Active**
Overview: [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
Description: Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, NEMA L6-30, 30A, 240V, 0.61m (2.0') Cord Length



Documents:
[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification	
UL	E66308
General	
Product Family	Power Distribution
Series	130153
Enclosure Rating	NEMA 6P
Exclude SD Check	Yes
GFCI Reset	Automatic
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	Ground Fault Circuit Interrupter (GFCI) Products
Product Literature Order No	987650-7737
Product Name	Super-Safeway
Receptacle Type	N/A
Type	GFCI Industrial Duty, Single Phase
UPC	78678888313
Physical	
Cord Diameter	13.00mm (.512")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Number of Receptacles	1
Packaging Type	Bag
Electrical	
Cord Type	10/3 SJEOOW
Current - Maximum per Contact	30.0A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	NEMA L6-30
Voltage - Maximum	240V
Material Info	
Engineering Number	30053-1A

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130153](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION