

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130147-0098](#)
Status: **Active**
Overview: [Watertite® Wet-Location Wiring Solutions](#)
Description: Watertite® Connector for Male Receptacle with Locking Blade, Single Flip Coverplate, 2 Pole/3 Wire, NEMA L6-30, 250V, F4

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family	Wiring Devices
Series	130147
IP Rating	IP67
NEMA Configuration	NEMA L6-30
Overview	Watertite® Wet-Location Wiring Solutions
Product Literature Order No	987650-8067
Product Name	Watertite®
Receptacle Type	Single
Specialty	N/A
Type	Connector
UPC	78678871407
Woodhead	Yes

Physical

Cord Grip Body Size	F4 1"
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Locking Blade	Yes
Poles	2-pole/3-wire

Electrical

Cord Type	N/A
Current - Maximum per Contact	30A
GFCI	No
Lighted Connector	No
Voltage - Maximum	250V

Material Info

Old Part Number 29W48MB



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[130147Series](#)