

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301430125](#)
Status: **Active**
Overview: [Watertite® Wet-Location Wiring Solutions](#)
Description: Watertite Cordset 12 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA 5-20 125V



Series image - Reference only

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
UL E38085

General

Product Family Wiring Devices
Series [130143](#)
IP Rating IP67
NEMA Configuration NEMA 5-20
Overview [Watertite® Wet-Location Wiring Solutions](#)
Product Literature Order No 987650-8067
Product Name Watertite
Receptacle Type Single
Specialty N/A
Type Cordset
UPC 78678871007
Woodhead Yes

Physical

Cord Grip Body Size F2 1/2"
Flange No
Flip Lid No
Gender Male-Female
Length 15.24m (50.0')
Locking Blade No
Poles 2-pole/3-wire

Electrical

Cord Type 12/3 SOOW
Current - Maximum per Contact 20.0A
GFCI No
Lighted Connector No
Voltage - Maximum 125V

Material Info

Engineering Number 14W33B123

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130143](#) Series