

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1210640900

Status:

Active

Overview:

mPm® DIN Valve Connectors

Description:

mPm® DIN Valve Connector, Form A, PG9 Internal Threads, 2 Pole Plus Ground with R0 Circuit, 230V, VDR Indicator, Black Nitrile Gasket

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Field Attachable / Accessories
Series	121064
Form	A
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	mPm® DIN Valve Connectors
Product Name	mPm®
Type	Field Attachable Connector
UPC	883906331856
Physical	
Cable Diameter	N/A
Coupling Type	Internal Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Orientation	90° Angle
Pitch - Mating Interface	18.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	230V
Material Info	
Engineering Number	S53209NR051

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Contained Per - ED/01/2017 (12 January 2017) 2,4-Di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p

Halogen-Free Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

121064 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION