

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1210120007](#)
Status: **Active**
Overview: [mPm® DIN Valve Connectors](#)
Description: mPm® DIN Base, Form A, B14 Base, 2 Pole Plus Ground Terminal, 250V AC/300V DC, Black Nitrile Gasket with Screw

Documents:

Drawing (PDF)	Test Summary STR-1467-001 (PDF)
Packaging Specification PK-121013-B14-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Field Attachable / Accessories
Series	121012
Form	A
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	mPm® DIN Valve Connectors
Product Name	mPm®
Type	Field Attachable Connector
UPC	883906322168

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Orientation	Straight
Pitch - Mating Interface	18.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC / 300V DC

Material Info

Engineering Number	B143000N2
--------------------	-----------

Reference - Drawing Numbers

Packaging Specification	PK-121013-B14-001
Sales Drawing	SD-121012-001
Test Summary	STR-1467-001

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[121012](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION