

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130105-0064](#)
Status: **Active**
Overview: [Specialty Lighting](#)
Description: Watertite® Wet Location 100W Spotlight with In-line Transformer, Screw Release Guard, 14-/2 SOOW, Overall Length 7.62m (50.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
 Series [130105](#)
 NEMA Configuration NEMA 5-15
 NEMA Rating NEMA 4X
 Outlet None
 Overview [Specialty Lighting](#)
 Product Literature Order No 987650-8052
 Product Name Watertite®
 Type Specialty Light
 UPC 78678861572
 Woodhead Yes

Physical

Cord Length - Primary 3.04m (10.0')
 Cord Length - Secondary 15.24m (50.0')
 Depth N/A
 Duty Wet Location
 Guard Included No
 Guard Type N/A
 Height 127.00mm (5.000")
 Length 228.60mm (9.000")
 Material - Guard #10 Gauge Vinyl Coated Steel
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Quartz Halogen
 Cord Type - Primary 16/3 SOOW
 Cord Type - Secondary 14/2 SOOW
 Lamp Type PAR36
 Lamp Wattage - Maximum 100W
 Lumens 1000
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ
 Voltage (Secondary) - Maximum 12V AC

Material Info

Old Part Number 1691-12B



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[130105Series](#)