


T9J8

PART	MOLD NO	Rev NO	Alteration Causation	Date
		①		
		②		
		③		



1. CABLE:UL1007 26AWG JACKET PVC OD=1.0mm
2. PLASTIC COVER; ABS GREY COLOR
3. CONN;RJ45 8P8C JACK CRIMP TYPE CONTACT PIN GOLD FLASH
4. CONN;DB9F SHELL PLATED NICKEL, CRIMP TYPE CONTACT PIN GOLD FLASH
5. SCREW;#4-40UNC PLATED NICKEL L=37MM

ROHS COMPLIANCY

ELECTRICAL TEST

- 1)100% OPEN SHORT&MISS WIRE TEST
- 2)INSULATION RESISTANCE:DC 5V 1M OHM/MIN
- 3)CONDUCTOR RESISTANCE: 1 OHM/MAX

A	T
1	BLUE
2	ORANGE
3	BLACK
4	RED
5	GREEN
6	YELLOW
7	BROWN
8	WHITE

STANDARD TOLERANCE LIMITS UNLESS OTHER SPECIFIED		
RANGE	TOLERANCE	
>0-6	±0.08	±0.14
>6-30	±0.10	±0.20
>30-120	±0.20	±0.30
>120-300	±0.30	±0.40
>300-600	±0.40	±0.50

單位	MM	比例	1:1	LKG INDUSTRIES			
圖法	圖號	頁數	1/1	dba PHILMORE MFG. / CARTEF			
文件編號				客戶	A007	制圖	CHENJUN
庫力昂料號				產品料號	T9J8B	審核	
出圖日期	2011.06.21			版次	1.0	核准	