

Bulgin is widely recognised as a leading manufacturer of environmentally sealed connectors and components. With over 95 years of experience in the industry, Bulgin continues to innovate and develop products and services to cater for its global customer base across a variety of markets.

EXPlora Series 900 Series 400 Series 6000 Series 4000 Series Vandal Switches Slide Switches Antimicrobial Switches Indicators

EXPlora Series

The EXPlora range is most suited to manufacturers of ancillary electrical equipment such as motors, pumps and lighting equipment.
These operate in ATEX Zone 2 environments where hazardous or explosive atmospheres can be caused by flammable gases, vapours or combustible dusts.



900 Series

Our most high powered connector in the Buccaneer range capable of up to 32A, 600V ac/dc rating. Sealed up to IP68, the 900 Series features a secure screw thread lock to ensure robust high voltage connections.



Standard Series

Tried and tested, the Standard Buccanner is one of our most popular waterproof connectors in the industry today. IP66, IP68 and IP69K rated, these power and data connectors have been designed into a wide range of markets such as Industrial and Marine, setting the gold standard for dust and waterproof circular connectors.

Quick Points

- Screw coupling
- Poles 2, 3, 4, 6, 7, 9, 12, 25
- Plug or Socket
- 1-12 Amp, 50-250V ac/dc
- 3.5-9mm cable acceptance
- Overall diameter 38mm

Data - Ethernet Buccaneer

- Single or double ended
- Standard lengths: 2m, 3m & 5m
- PUR jacket cable
- Supplied with shielded RJ45 plug
- S-FTP cable construction
- Wiring configuration to 568-B Exceeds EIA/TIA Cat 5e

Data - USB Buccaneer

- Screw coupling
- Available in various different A, B
- configurations

Body Style & Part

Flex Connector PX0731

Flex In-line PX0732

Prewired Flex Connector PX0700

Front Panel Mount PX0730/P

Rear Panel Mount PX0709

PCB Mount PX0707

Sealing Cap Accessory PX0734, PX0733

Data - Ethernet Buccaneer

Ethernet Patch Cord Flex Connector PX0836, PX0837, PX0838

Ethernet Re-wireable Flex Connector

PX0834

Ethernet Panel Mount PX0833

Ethernet Flanged Panel Mount

Ethernet PCB Mount PX0839

Shield Back Shell Accessory

PX0888

Data - USB Buccaneer

Sealed USB Cables - Single Ended PX0840

Sealed USB Cables - Double Ended

USB Front Panel Mount PX0842

USB Panel Mount with lead PX0844

USB Rear Panel Mount PX0848

Industries

Data & Telecoms

Industrial

Transport & Infrastructure

The Range



PX0731





PX0732





PX0730/P



PX0709





PX0765/S



PX0756





PX0700



PX0733 PX0734



PX0777



PX0836



PX0834



PX0833



PX0839/90



PX0839/IDC

PX0849/B





PX0870



PX0888



PX0835



PX0840/A



PX0841/AB



PX0840/B



PY08/12/A

PX0842/B

PYOR/10/A



PYOR48/A PX0848/B



PY08/15/A PX0845/B



PY08/13/A PX0843/B



Accessories



PX0835



PX0852





A compact and versatile connector within the Buccaneer range, the 400 series is ideal for designs requiring a small footprint. Taking a selection of great features and specifications from the larger Buccaneer family, the 400 series condenses them into a compact form factor giving engineers greater flexibility.

Quick Points

Power

- Screw coupling
- Flex Cable Connector
- 2, 3, 4, 6, 8, 10 and 12 pole
- Pin or Socket inserts
- 1-8A, 50-250V ac/dc
- Cable acceptance 3-7mm
- Overall diameter 19mm

Data (Mini USB)

- Screw coupling
- Single ended sealed cable assembly
- Fully overmoulded construction (Flex Connector)
- Available in 2, 3 & 4.5m lengths
- 5 way crimp, for use with PC header or rear panel mounting connector with leaded 5 way header (leaded panel mount versions)

Data (SMB & Wireless Antenna)

- Screw coupling
- Single ended sealed cable assembly
- Fully overmoulded construction (Flex Connector)
- Available in 2, 3 & 4.5m lengths
- 5 way crimp, for use with PC header or rear panel mounting connector with leaded 5 way header (leaded panel mount versions)

Industries

Body Style & Part

Power

Flex Connector PX0410

Flex In-line PX0411

Prewired Flex Cable Connector PX0400, PX0401, PX0402

Panel Mount

PX0412, PX0413

Sealing Cap Accessory

PX0480, PX0480/1, PX0481, PX0484

Data (Mini USB)

Flex Connector Standard & Mini A to B PX0441, PX0442

Flex Connector Mini B to Standard A or Mini A

PX0444

Front Panel Mount Mini B type or Mini AB type

PX0443, PX0456

Rear Panel Mount Mini B type or Mini AB type

PX0446, PX0457

Rear Panel PCB Mount Mini B type or Mini AB type

PX0447, PX0458

Data (SMB & Wireless Antenna)

Re-Wireable Flex Connector

PX0415/1

Pre - Wireable Flex Connector

Panel Mount

PX0414

Sealing Cap

PX0480, PX0481, PX0485

Rear Panel PCB Mount Mini B type or

Mini AB type

PX0480 PX0480/1 PX0481 PX0484

SMB Antenna

PX0407, PX0408, PX0409

SMB 90 Degree Angled Antenna PX0407/90, PX0408/90, PX0409/90

Marine

Automotive

Medical

The Range





























PX0442

PX0415/1

PX0414

PX0412

PX0413

PX0446













PX0447

PX0400

PX0480/1 PX0481 PX0484

PX0443 PX0456

PX0485 PX0480 PX0484

PX0407



Designed and independently tested to IP66, IP68 & IP69K standards, the rapid twist lock 6000 series connectors are ideal for applications where ingress of dust and water must be avoided and where ease of connection. space and appearance are important requirements.

Quick Points

Power

Metal & Plastic versions

- Push/pull coupling
- Flex Cable Connector
- Mates with all other body styles
- 2, 3, 8, 16 & 22 pole
- Plug or Socket
- 16A, 277 V (max)
- 4-10mm cable acceptance
- Overall diameter 32mm

Data (Ethernet)

Plastic & Metal versions

- Push/pull coupling
- Re-wireable flex Cable Connector
- Two versions for PE and PUR jacket cable
- Supplied with shielded RJ45
- Sealed through panel
- Cat 5e shielded coupler
- Standard patchcord can be plugged into rear
 Version with earth wire available

Data (USB)

Plastic version Only

- Push/pull coupling
- Single and double ended sealed
- cable assembly
- Flex connector available in 2m. 3m. and 5m lengths
- Leaded with 5 way crimp connector (lead version only).

Body Style & Part

Power

Flex Connector PXP6010, PXM6010

Flex In-line PXP6011, PXM6011

Panel Mount PXP6012, PXM6012

Sealing Cap Accessory PXP6081, PXM6081 PXP6082, PXM6082 PXP6083, PXM6083

Data (Ethernet & USB)

Ethernet Flex Connector PXP6034, PXM6034

Ethernet Panel Mount PXP6033TP, PXM6033TP

Ethernet Overmoulded Flex PXP6037, PXP6038

USB A/B Flex Connector PXP6040, PXM6041

USB Panel Mount PXP6042

USB Panel Mount with lead PXP6043

Industries

- Marine - Automotive - Renewable - Recreation & Leisure -

The Range



PXM6010

PXP6034





PXM6011

PXM6034

PXP6033



PXM6012







PXP6010













PXM6040/A

PXM6033







PXM6042/A PXM6042/B

PXM6043/A PXM6043/B



7000 Series

Available in plastic and metal body constructions, the 7000 Series Buccaneer connectors combine the easy use of a quick coupling mechanism with proven environmental sealing for signal and mains power.

4000 Series

The 4000 Series brings high power and data in a compact form factor. Its small and mighty characteristics make it ideal for power and data applications across a wide variety of markets.

Quick Points

Power

- Metal & Plastic versions
- Rapid twist locking
- 2, 3, 6, 10 & 32 pole
- Plug or Socket - 25A, 600 V (max)
- 5-15mm cable acceptance
- Overall diameter 42mm

Body style & part

Power

Flex Connector - PXP7010, PXM7010
Flex In-line - PXP7011, PXM7011
Panel Mount - PXP7012, PXM7012
Sealing Cap Accessory - PXP7081, PXP7082, PXM7081, PXM7082, PXM7083

Industries

- Marine - Industrial - Automotive - Oil & Gas - Transport & Infrastructure -

The Range













PXM7010

PXM7011

PXM7012

PXP7010

PXP7011

PXP7012

Quick Points

Power

- Rapid twist lock coupling
- 3, 8 & 12 pole power up to 600V, 13A
- Sealed to IP66, IP68 and IP69K when mated
- Solder and crimp contacts available

Data (Micro USB)

- Data rates up to 480Mbs
- USB V2.0 performance
- Secure, proven locking systemTamperproof Construction
- EN60068-2-52 Test Kb Salt Mist
- (Cyclic) Marine Severity Level 1

Renewable

Industries

Recreation & Leisure

Data & Telecoms

.

Marine

Body Style & Part

Power

Flex Connector PX04010

Flex In-line PX04011

Panel Moun

Sealing Cap Accessory
PX04081 PX04082 PX0408

Data (Mini USB)

Flex Connector Standard A to Micro B PXP4040

Rear Panel Mount Micro B PXP4043

Sealing Cap Accessory PXP4081, PXP4083

The Range





PXP4011



PXP4013







PXP4040

PXP4043



PXP4010






PXP4081 PXP4089 PXP4082 PXP4083

PXP4089



Filters

Designed to reduce conducted mains borne EMI, this extensive range provides many solutions to EMI problems. To meet individual design requirements the filters are available with one standard filter circuit.



Power Entry Modules

Quick Points


C14 Inlet

available for security of screw fixing.

- Vertical and horizontal arrangement

- Compact single rectangular mounting hole, flange fixing alternative

With over 26,000 combinations, Bulgin's Polysnap mains power inlet modules offer a very adaptable and flexible solution to panel design. They allow combinations of mains inlets and outlets, filtered inlets, switches, fuseholders, voltage selectors and indicators to be mounted in either horizontal or vertical format bezels ready for quick snap-fit assembly.



Industries

Medical

Connectors

A full range of quality mains rated connectors conforming to IEC and EN 60320 specifications carrying UL, CSA, VDE and other approvals. With electrical ratings up to 20A, 250V (UL) these connectors offer solutions to most mains powered applications.

Quick Points

- Flange fixing, snap to panel and PCB mounting options 250V ac, 10A up to 20A
- 2.8 solder tabs, 4.8 and 6.3 fast on tabs, screw terminal and PC spill versions.
- Accessories include insulating boots, retaining clips and safety covers.
- Additional colours available

Industries

Medical

Data & Telecoms

Industrial

The Range









PX0575



PX0579



PX0587

PX0587/SE

PX0588





PX0580/PC







PF0030



PX0597





PF0011







PX0686/SF



PX0716



PX0690







PX0686



















PX0793 Termination

















KT0006



PX0592



12075

PX0597

PX0596

PX0598

PX0591

PX0578



0717-1-P

0717-1S

Fuseholders

Bulgin's extensive range of fuseholders are designed to give the degree of protection demanded in today's sophisticated electronic equipment. Carrying worldwide safety approvals from UL, VDE, CSA and IMQ, all types are manufactured from high grade flame retardant nylon and polyester materials.


Quick Points

- Designed primarily for 5 x 20mm and 6.3 x 32mm size fuses Protection against shock to categories PC1, PC2 and PC3.
- In-line, PCB mounting and panel mounting (screw or snap fit) options available
- Terminal options for solder, 2.8mm, 4.8mm or 6.3mm tabs or PC spills. Front of panel seal up to IP68 in both 5 \times 20mm and 6.3 \times 32mm size fuses.
- Captive drawer, screw cap and bayonet cap Fuse carrier styles
- Screwdriver release and screw cap with finger release options

Industries

Recreation & Leisure

Data & Telecoms



Battery Holders

Manufactured from quality mouldings and metal components to ensure a secure and reliable connection, Bulgin's battery holder range caters for battery sizes; AAA(RO3), AA(R6), C(R14), D(R20), PP3(6R61) and CR123, accommodating 1, 2, 3 or 4 cells.





Vandal Switches

Manufactured from Stainless Steel, Bulgin's extensive range of vandal resistant security switches are designed with a high resistance to wear and tear, corrosion and harsh use in potentially hostile environments such as access control applications.

Quick Points

- Front and rear panel mounted versions

 Vandal switches available in prominent, domed and low profile
- Various switching options such as latching, push on push off, action.
- IP66, 68 & 69K front panel sealing options Dot and ring LED illuminated versions
- Illumination voltages 6, 12 and 24V sources,
- Variety of illumination colours and are now available with front and rear of panel sealing options.

Industries

Transport & Infrastructure

Industrial

Recreation & Leisure

The Range













MP0012/1

MP0012

MP0013 MP0033

MP0013/2 MP0033/2

MP0016

MP0022











MP0031



MP0027

MP0027/2

MP0027/3

MP0031/2















MP0037/3



MP0038/2

MP0038

MP0042/1

MP0042/2















MP0042/3

MP0045/1/D1

MP0045/1/D2 MP0045/1E

MP0045/3E

MP0050















MP0050/2







MP0031/3



MPB307





MPI001/RP

MPI001



MPI002/FI

MPI002

VS0001

VS0002

8300

Piezo Switches

Unlike traditional switches, Piezo Switches are designed to withstand the harshest of environments. With no moving mechanical parts, they are extremely durable and able to withstand millions of actuations whilst requiring little to no maintenance.

Quick Points

- Piezo switches have no moving mechanical parts which offers excellent endurance and durability
- Stainless Steel and Aluminium body types
- Ratings up to 1A, 24V ac/dc
- Illuminated and Non-Illuminated variants available
- Latching and momentary actions
- Sealed to IP68 and IP69K ratings

Industries

Marine

Medical

The Range





MP7016 MPZ019 MPZ022

MP7I019 MPZI022 MPZI022L

Slide Switches

With up to 5 switching positions as well as multiple terminal, circuit and slider options, Bulgin's board mounted power slide switches can be configured to suit your needs. We also offer a wide range of voltage selector types that can be either snapped into a panel or flange mounted.

Quick Points

- Ratings up to 16A, 250V ac
- PCB and solder terminals
- Voltage Selector Models
- Snap in and flange mounting
- 2, 3, 4 and 5 position
- Choice of circuits
- Choice of actuators

Industries

Small Domestic Appliances

Kitchen Appliances

The Range





2000

Rocker Switches

With numerous configurations and available options, Bulgin's extensive line of rocker switches are the primary choice for many globally recognized OEM's.



- Available types: Ultra-thin, Miniature, Twin unit, Miniature round and Standard
- Rating from 10A, 250V ac up to 20A, 277V ac
- Single & double pole variants available
- Push-on, solder & PCB terminals
- Illuminated and non-illuminated options
- High in-rush (ON-OFF types)
- Matching Indicators
- Splash resistant options
- Choice of bezel styles and sizes, panel cut-outs and actuators
- Choice of switching circuits including 3 position

Industries

Brown Goods

Electronics

Medical

Recreation & Leisure

The Range



Push Button Switches

Bulgin's broad line of pushbutton switches are available in various sizes. and configurations. This includes a variety of illumination and terminal options as well as several with high inductive power ratings suitable for motor driven applications. These switches can be found in many markets including home appliances, commercial, medical, audio and security.

Quick Points

- Miniature, round and rectangular push button switches available
- Ratings up to 16A, 250V ac
- Latching and momentary actions
- Choice of actuators (custom option also available)
- Square and Round Mounting Styles

Industries

Industrial

Automotive

Medical

Security

Domestic Appliances

The Range









7000

8300

Toggle Switches

Well known for their quality and reliability, Bulgin's toggle switches are cost effective solutions to many existing applications. Independently tested for shock and vibration along with operation to -40°C, these switches offer features at an attractive price point often well below that of the existing competition.

Quick Points

- Nylon and Metal switch variants
- Multiple Lever Options
- Ratings up to 20A, 250V ac 277V ac
- IP67 panel seal versions, supplied complete with gaskets (3900 Series - All Variants)
- Single and double pole
- Choice of circuit options including 3 position and momentary
- Mounting hole: 12.7mm diameter.
- Sealing accessories available
- Quick Connect, Solder, Screw and PCB Termination Options

Industries

Commercial Transportation

Industrial controls & Instrumentation

Specialist Vehicles

Consumer Goods

The Range





3900

1700

Refrigerator Door Switches

Long recognised as a leader in refrigerator door switches, Bulgin's wide range of types and configurations will suit almost any need. With both double pole and single pole options, our switches are not only ideal for traditional refrigerator and freezer applications but can and have been used in a variety of door applications as well.

Quick Points

- Switch rating from 0.2A, 250V ac up to 5A, 250Vac
- Splash resistant variants
- Choice of actuators
- Momentary on and momentary off switching

Industries

Domestic Appliances

The Range











0305

3005

3100

3140

Antimicrobial Switches

Among the most innovative additions to our product offering are BioCote antimicrobial switches, BioCote is a silver ion product that is added to the molding process so it is integral to the plastic and will not wear off. Switches made with the BioCote additive are infused with antimicrobial properties that prevent the spread of dangerous microbes from multiple users activating the switch.



- BioCote antimicrobial material
- Single and double pole options
- Ratings from 15A, 250V ac to 20A, 277V ac
- Choice of bezel styles and sizes
- Choice of panel cut-out sizes
 - 19.3 x 12.9mm (8500 & 8300 Series)
 - 30.1 x 22.2mm (6050 Series)
 - 6 Different mounting sizes/styles (1550 Series)
- Illuminated and non-illuminated options available

Industries

Medical

Food Processing



Indicators

This range of panel mounting LED indicators consists of many different types of LED's, bezel styles and colours. The range has developed to meet the many different needs of panel design including IP66 environmentally sealed versions for use where a front panel seal is needed.

Quick Points

- Complement the Bulgin vandal resistant switches similar profiles with stainless steel bodies.
- Sealing to IP67 and are built to withstand harsh environments.
- Various LED and illuminated colour options
- Prominent or recessed styles
- Wide viewing angle option
- Termination options include Wire Leads, 2.8 Tabs, 4.8 or 6.3 QC termination

Industries

Marine

Medical


Transport and Infrastructure

Industrial



LED Lampholders

Among the smallest and most versatile products within our indicator range are LED Lamps and Lampholders. Quite small in size, the LED housings we offer incorporate an LED and allow it to be mounted in a panel. We also offer re-lampable LED lampholders which can be supplied with or without LED's. These products are ideal where a reliable, long life indication in a small package is needed.



IP Rated Indicators and LED Lampholders

Bulgin has a long history of offering sealed, robust products and our indicators are no exception. Available in six popular sizes and styles, the indicators are all sealed to IP67 and can be fitted with Neon, LED or filament lamps. Several of our larger Low Voltage (IP67) and small LED lampholders (IP66 and IP67) are also available with IP sealing. Both types can be fitted with or without lamps. All of these products are great for any environment where moisture is a concern.








We've got you covered

Our components are available through a large network of National and International Distributors Worldwide. Search for our stock at - www.bulgin.com/distributors.html



EMEA

Bulgin Broers Building, JJ Thomson Avenue, Cambridge CB3 0FA UK Tel: +44 (0)1223 371 000 Fax: +44 (0)1223 350 642 info@bulgin.com

The Americas

Bulgin 11930 Hamden Place Santa Fe Springs CA 90670 USA Tel: +1 760-343-3650 Fax: +1 760-343-3345 info@bulgin.com

APAC

Bulgin 3 Temasek Avenue Centennial Tower Level 34 Singapore 039190 Tel: +65 6549 7161 info@bulgin.com

