Steel City®

Square Boxes and Accessories



52151-1/2 & 3/4-EWP

- Popular 4" Square Boxes and Switch Boxes.
 Pre-Insalled 10½" Insulated Pigtails.

Cat. No.	Box Type Included	Pigtail Type Included	Std. Ctn.
52151-1/2 & 3/4-EWP	521511234EW	10½"	50
52151-1/2 & 3/4-P	521511234	10½"	50
52151-1/2 & 3/4-EP	521711234E	10½"	50
52151-XP	52151X	10½"	50
52151-CVNP	52151CVN	10½"	25
_XWOWP	LXWOW-25	10½"	25
LXVP	LXV-25	10½"	25
CXWOWP	CXWOW	10½"	25
CXWVP	CXWV	10½"	25
CXP	CX	10½"	25









4" Square Covers					
Cat. No.	Raised	Description	Cu. In. Cap.	Std. Ctn.	
52-C-1	-	Flat, blank	-	100	
52-C-3-25	5/8"	Center blanked with tapped ears on 23/4" centers	4.3	25	
52-C-3-1/2-25	1/2"	Center blanked with tapped ears on 23/4" centers	3.5	25	
52-C-3-3/4	3/4"	Center blanked with tapped ears on 223/32" centers	4.3	25	
52-C-3-1	1"	Center blanked with tapped ears on 223/32" centers	5.8	25	
52-C-3-1-1/4	11/8"	Center blanked with tapped ears on 223/32" centers	7.3	25	
52-C-6	-	Flat, with ½" KO	-	100	



SH 1/2 & 3/4

Swivel Hangers						
Cat. No.	Bar Lgth. (in.)	Description	Slot (in.)	Std. Ctn.		
SH 1/2 & 3/4	-	Swivel Hanger for 4" Square Boxes	-	25		

UL Listed for 50 lb. Fixture Support.





52-C-0





52-C-14



4" Square Device Covers					
Cat. No.	Raised	Description	Cu. In. Cap.	Std. Ctn.	
For single device					
52-C-0	_	Flat	_	25	
52-C-62	1/4"	Keyed for plaster	1.5	25	
52-C-10	1/4"	Offset, keyed for plaster	1.0	25	
52-C-13	1/2"	·	3.0	50	
52-C-14	3/4"		5.0	50	
52-C-14-5/8	5/8"		4.0	50	
52-C-15	1"		7.0	25	
52-C-16	11⁄4"		8.3	25	
52-C-36	1/4"	For dry wall construction	1.0	25	

