Search Product:

Submit

[Advanced]

- Adapters & power supplies
- Batteries & chargers
- Cables & accessories
- Connectors
- Consumer products & pc acc.
- Electronic components
- High-q tools & dmm's
- Led products & lamps
- Light products
- Loudspeakers & pa systems
- Perel tools
- Security products
- Velleman kits & oscilloscopes

HIGH - Q TOOLS & DMM'S > PANEL METERS > PANEL METERS - DIGITAL >

DIGITAL PANEL METER LED - 5V DC

Order Code: PMLED/5

Features

- 3 1/2 LED digital panel meter
- single 5V DC operation
- high input impedance: > 100Mohm
- optional resistor set: PM/RES

ROHS Info

Specifications

- display: 3 1/2 digit LED
- input sensitivity: 200mV FS
- power supply: 5V DC
- decimal point selection: with wire jumper
- automatic polarity indication
- figure height: 0.56"
- sampling rate: 2 - 3 readings / sec.
- guaranteed zero reading for 0V input
- high input impedance: > 100Mohm
- accuracy: ± 0.5%
- power consumption: 50 - 60mA
- size: 2.7" x 1.7"

Files

- EN - FR - NL - ES - DE

Stock Info

- Inner carton:
- Outer Carton: 100
- EAN Barcode: 5410329301606
- Packaging: Box (Carton)

(C) 2005 Velleman Components N.V.
[Disclaimer]